

# Flush Furniture Feed Series, Through Floor Fitting, 3 Service, Furniture Feed, Gray Finish

By Hubbell Wiring Device-Kellems  
Catalog # [PT73FFSDGY](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush Furniture Feed Series, Through Floor Fitting, 3 Service, Furniture Feed, Gray

## Performance

- Electrical - Fire Resistance Rating - 4-Hrs. (D900)
- Electrical - UL Installation - Min. of 2 feet on centers and not more than one unit per 65 sq. ft. of floor area
- Mechanical - Max. Cu Cross Section - 3/4 in. EMT .0470 sq. in. and 1/2 in. Feed Through .0250 sq. in.

## General

Catalog Number	PT73FFSDGY
Construction	Fabricated
Cover Type	Furniture Feed
EU RoHS Indicator	No
Finish Type	Gray
Item Type	3" Fire-Rated Poke-Through Component
Material	Composite
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 3/4" & (2) 1/2" Threaded Hub Hub 3 Service
OEM Brand Name	Hubbell Wiring Device-Kellems
Specifications	<ul style="list-style-type: none"><li>• Conduit Cover - Aluminum</li><li>• Cored Hole - 3" (76.2) diameter</li><li>• Floor Thickness - 2 1/4 in. to 7 in. (57.2 to 177.8)</li></ul>



Style  
UPC

• Service fitting - Flush painted aluminum service fitting and carpet flange  
In Floor Fitting  
783585494227

## Conductor Related

Cable Entry Threaded Hubs

## Certifications And Compliance

Buy America(n) Qualified TAA Compliant (All status valid till December 2024)

Industry Standard(s)

- cULus Listed
- Meets ADA Standards
- UL 514A Listed

## Logistics

Carton Quantity 1

## Product Assets

[Catalog Page - WDK P-33 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Installation Manuals - WIRING\\_PD1909\\_INSTALLINST](#)  
[Literature - Delivery Systems Product Guide](#)  
[Specifications - PT73FFSDGY](#)  
[Warranty - Industrial & Commercial Products](#)