

## Combination Devices, Residential Grade, 1) Single Pole Toggle, 1) Three Way Toggle, 15A 120V AC, Self Grounding, Side Wired

By Hubbell Wiring Device-Kellems  
Catalog # [RC103AL](#)



Switches and Lighting Controls, Combination Devices,  
Residential Grade, 1) Single Pole Toggle, 1) Three Way Toggle,  
15A 120V AC, Self Grounding, Side Wired, Almond

### Features

- Quiet snap action mechanism
- Self-grounding staple is standard
- Elongated strap with continuous plaster ears

### Application

Residential

### General

Action	Snap Switch
Actuator	Toggle
Catalog Number	RC103AL
Contact Configuration	Two Position
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Switch Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	1) Single Pole, 1) Three Way
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact

UPC 883778109928

### Dimensions

Display Size Standard Size

### Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	120 VAC
Wattage	1800

### Logistics

Carton Quantity 10

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - RC103AL AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2132\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_RC103\\_DRAWINGS\\_PDF](#)  
[Specifications - RC103AL](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)