

Combination Devices, Residential Grade,
Decorator Series, 1) Single Pole Rocker, 1)
Tamper Resistant Single Receptacle, 15A
120V AC, Side Wired

By Hubbell Wiring Device-Kellems
Catalog # [RCD108ALTR](#)

Switches and Lighting Controls, Combination Devices, Residential
Grade, Decorator Series, 1) Single Pole Rocker, 1) Tamper Resistant
Single Receptacle, 15A 120V AC, Side Wired

Features

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- Self-grounding feature is standard

Application

Residential

Specifications

Environmental Conditions Indoor Dry Unless Protected By
Additional Means

Conductor

Number Of Poles 1) Single Pole

Configuration

Contact Configuration Two Position

Current

Amperage Rating 15 A
Current Rating 15 A
Voltage Rating 125 VAC
Wattage 1875
Connectivity Side Wired
Current / Amperage Rating 15 A



Contact Rating 15A

Dimensions

Display Size Standard Size

General

OEM Brand Name Hubbell Wiring Device-Kellems
UPC 883778302336
Material - Mounting Hardware Mounting Screws
Item Type Decorator Switch and Receptacle
Combo Devices

Logistics

Carton Quantity 10

Operational

Actuator Rocker
Action Snap Switch
Operating Cycles 30,000 Minimum
Operating Temperature Max Continuous- 60 Degrees C,
Minimum- -20 Without Impact

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)