



20A Kitchen Counter Receptacle, Surface Mount, Nickel

By Hubbell Wiring Device-Kellems
Catalog # [RCT220NI](#)

20A Kitchen Counter Receptacle, Surface Mount, Nickel



Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

Application

Power on Counter Top

General

Color	Nickel
Construction	Fabricated
Construction Material - Main	220 Meunt
Material	220 Meunt
Mounting Type	In Kitchen Counter Top
Number Of Outlets	1 Duplex
Number Of Poles	2
Series	Countertop Receptacle
Size	Standard Sized
Style	Surface
Sub Brand	Furniture Boxes
Type	<ul style="list-style-type: none">• Power Only• Power Only
UPC	883778309526

Dimensions

Dimensions	4.20 in x 4.20 in x 6.48 in
Height	6.48 in
Length	4.20 in
Width	4.20 in

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Conductor Related

Cable Entry	Kos in Bottom
Number Of Wires	3

Certifications and Compliance

Industry Standard(s)	UL
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD2741_INSTALLINST](#)
[Literature - Property Management | Home Enhancements | Innovation and Convenience](#)
[Literature - Differentiate Your Property](#)
[Literature - Multifamily Property Tech Enhancements](#)
[Literature - Residential Catalog](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Hubbell Tri-Power Pop-Up Receptacle](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK-RCT220NI-SPEC-EN | REV 1/2024