

Signal and Control, Linkosity,
Female Receptacle, 4-Wire, 10A
600V AC, PA Wire Code, 5' Length

By Hubbell Wiring Device-Kellems
Catalog # [RF1004PA005](#)

Signal and Control, Linkosity, Female Receptacle, 4-Wire, 10A
600V AC, PA Wire Code, 5' Length

Features

- Linkosity4-Wire
- 10A 600V AC

Application

Power and Control Integration

General

Catalog Number	RF1004PA005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585128108

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV



Wattage	6000
---------	------

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RF1004PA005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2039_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_RF1004PA005_DRAWING_PDF](#)
- [Specifications - RF1004PA005](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)

