

HUBBELL
Wiring Device-Kellems

LINKOSITY, Female Receptacle, 4-Pole, 10A, 10' Length

By Hubbell Wiring Device-Kellems
Catalog # [RF1004PA010](#)

LINKOSITY, Female Receptacle, 4-Pole, 10A, 10' Length



General

Application	Power and Control Integration
Catalog Number	RF1004PA010
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585243160

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV
Wattage	6000

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RF1004PA010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2039_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_RF1004PA010_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand