

10A, 4W, Female Receptacle, 1'

By Hubbell Wiring Device-Kellems
Catalog # [RF1004PB001](#)

10A, 4W, Female Receptacle, 1'



Oh No!
IMAGE COMING SOON

Features

- 10A
- 4W1'

Application

Power and Control Integration

General

Catalog Number	RF1004PB001
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504438

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A

Current Rating	10 A
Voltage Rating	600V Max kV
Wattage	6000

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RF1004PB001 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2039_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Sales Drawings - WDK_RF1004PB001_DRAWING_PDF](#)
[Specifications - RF1004PB001](#)
[Warranty - Industrial & Commercial Products](#)