



Signal and Control, Linkosity, Female Receptacle, 4-Wire, 10A 600V AC, PM Wire Code, 5' Length

By Hubbell Wiring Device-Kellems
Catalog # [RF1004PM005](#)

Signal and Control, Linkosity, Female Receptacle, 4-Wire, 10A
600V AC, PM Wire Code, 5' Length



Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585131023

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV
Wattage	6000

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number Of Conductors	4

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Engineering Drawing - RF1004PM005 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2039_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_RF1004PM005_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RF1004PM005-SPEC-EN | REV 5/2023