



## 10A, 5W, Female Receptacle, 1'

By Hubbell Wiring Device-Kellems  
Catalog # [RF1005PE001](#)

10A, 5W, Female Receptacle, 1'



### Application

Power and Control Integration

### General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	5-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504476

### Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV
Wattage	6000

### Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number Of Conductors	5

### Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

### Logistics

Carton Quantity	50
-----------------	----

### Product Assets

[Engineering Drawing - RF1005PE001 AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2039\\_INSTALLINST](#)  
[Literature - WIRING\\_WLFVM034](#)  
[Literature - Linkosity Wiring System](#)  
[Literature - Pulp & Paper Solutions](#)  
[Sales Drawings - WDK\\_RF1005PE001\\_DRAWING\\_PDF](#)  
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-RF1005PE001-SPEC-EN | REV 5/2023