

10A, 5W, Female Receptacle, 1'

By Hubbell Wiring Device-Kellems
Catalog # [RF1005PG001](#)

10A, 5W, Female Receptacle, 1'



Oh No!
IMAGE COMING SOON

Features

- 10A
- 5W1'

Application

Power and Control Integration

General

Catalog Number	RF1005PG001
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	5-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504490

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV

Wattage 6000

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number of Conductors	5

Certifications And Compliance

Nema Rating Non-NEMA

Logistics

Carton Quantity 50

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RF1005PG001 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2039_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Sales Drawings - WDK_RF1005PG001_DRAWING_PDF](#)
[Specifications - RF1005PG001](#)
[Warranty - Industrial & Commercial Products](#)