



Linkosity, Receptacle 10A, 6P, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RF1006PE005](#)

Linkosity, Receptacle 10A, 6P, 5'



Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	6-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585505107

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV
Wattage	6000

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number Of Conductors	6

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Engineering Drawing - RF1006PE005 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2039_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_RF1006PE005_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RF1006PE005-SPEC-EN | REV 5/2023