

Signal and Control, Linkosity,  
Female Receptacle, 2-Wire, 20A  
600V AC, PE Wire Code, 1' Length

By Hubbell Wiring Device-Kellems  
Catalog # [RF2002PE001](#)

Signal and Control, Linkosity, Female Receptacle, 2-Wire, 20A  
600V AC, PE Wire Code, 1' Length

Features

- Linkosity2-Wire
- 20A 600V AC

Application

Power and Control Integration

General

Catalog Number	RF2002PE001
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585358284

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A



Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	2

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING\\_PD2033\\_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Specifications - RF2002PE001](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)