

Linkosity, 20A 2W, Female Receptacle, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RF2002PE005](#)



Linkosity, 20A 2W, Female Receptacle, 5'

Features

- Linkosity
- 20A 2W5'

Application

Power and Control Integration

General

Catalog Number	RF2002PE005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585409634

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV

Wattage	12000
---------	-------

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	2

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RF2002PE005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2033_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_RF2002PE005_DRAWINGS_PDF](#)
- [Specifications - RF2002PE005](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)