

Linkosity, Female Receptacle, 20A 5W

By Hubbell Wiring Device-Kellems
Catalog # [RF2005PB005](#)



Linkosity, Female Receptacle, 20A 5W

Features

- Linkosity20A 5W

Application

Power and Control Integration

General

Catalog Number	RF2005PB005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	5-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585409504

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A

Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number of Conductors	5

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RF2005PB005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2033_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_RF2005PB_DRAWING_PDF](#)
- [Specifications - RF2005PB005](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)