



Wiring Device-Kellems

Signal and Control, Linkosity, Female Receptacle, 4-Wire, 20A 600V AC, PA Wire Code, 1' Length, Super, Neutral/IG



By Hubbell Wiring Device-Kellems
Catalog # [RF2304PA001](#)

Signal and Control, Linkosity, Female Receptacle, 4-Wire, 20A 600V AC, PA Wire Code, 1' Length, Super, Neutral/IG

Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585524696

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number Of Conductors	4

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Engineering Drawing - RF2304PA001 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2194_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_RF2304PA_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RF2304PA001-SPEC-EN | REV 5/2023