

Linkosity, Female Receptacle, 20A Single, 6P, 10'

By Hubbell Wiring Device-Kellems
Catalog # [RF2306PB010](#)

Linkosity, Female Receptacle, 20A Single, 6P, 10'



Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	6-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585354859

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number of Conductors	6

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RF2306PB010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD1995_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - WIRING_WLFVM034](#)
[Sales Drawings - WDK_RF2306PB_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)

