

Linkosity, Female Receptacle, 20A Single, 6P, 30'

By Hubbell Wiring Device-Kellems
Catalog # [RF2306PB030](#)

Linkosity, Female Receptacle, 20A Single, 6P, 30'



General

Application	Power and Control Integration
Catalog Number	RF2306PB030
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	6-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585524320

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number of Conductors	6

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RF2306PB030 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1995_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Sales Drawings - WDK_RF2306PB_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand