



Linkosity, Hazardous Location, Female Receptacle, 20A 5-Wire

By Hubbell Wiring Device-Kellems
Catalog # [RF2705PB005](#)



Linkosity, Hazardous Location, Female Receptacle, 20A 5-Wire

Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	5-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585355856

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG
Conductor Type	Copper
Number Of Conductors	5

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Engineering Drawing - RF2705PB005 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2316_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_RF2705PB005_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RF2705PB005-SPEC-EN | REV 5/2023