



Wiring Device-Kellems

# Linkosity, 30A 4W, Female Receptacle, 10'

By Hubbell Wiring Device-Kellems  
Catalog # [RF3004PA010](#)



Linkosity, 30A 4W, Female Receptacle, 10'

## Application

Power and Control Integration

## General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504667

## Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V Max kV
Wattage	18000

## Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	4

## Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

## Logistics

Carton Quantity	50
-----------------	----

## Product Assets

- [Engineering Drawing - RF3004PA010 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2035\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_RF3004PA\\_DRAWING\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.