

Linkosity, Female Receptacle, 30A 4W, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RF3004PB005](#)



Linkosity, Female Receptacle, 30A 4W, 5'

Features

- Linkosity30A 4W
- 5'

Application

Power and Control Integration

General

Catalog Number	RF3004PB005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585116471

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V Max kV

Wattage	18000
---------	-------

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RF3004PB005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2035_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_RF3004PB_DRAWING_PDF](#)
- [Specifications - RF3004PB005](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)



A Hubbell brand