

Linkosity, Female Receptacle, 30A 4W

By Hubbell Wiring Device-Kellems
Catalog # [RF3004PB010](#)

Linkosity, Female Receptacle, 30A 4W



General

Application	Power and Control Integration
Catalog Number	RF3004PB010
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504674

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V Max kV
Wattage	18000

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RF3004PB010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2035_INSTALLINST](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Sales Drawings - WDK_RF3004PB_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand