



Wiring Device-Kellems

Signal and Control, Linkosity, Female Receptacle, 20A 2W, Super Neutral, Isolated Ground

By Hubbell Wiring Device-Kellems
Catalog # [RF7205PB005](#)



Signal and Control, Linkosity, Female Receptacle, 20A 2W, Super Neutral, Isolated Ground

Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	5-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585355672

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number Of Conductors	5

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

- [Engineering Drawing - RF7205PB005 AutoCAD Drawing](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_RF7205PB005_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RF7205PB005-SPEC-EN | REV 5/2023