

Linkosity, Receptacle 3A, 3P, 5'

By Hubbell Wiring Device-Kellems
Catalog # [RFR303PE005](#)

Linkosity, Receptacle 3A, 3P, 5'



Application

Power and Control Integration

General

Catalog Number	RFR303PE005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Female Receptacle
Material	Composite
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585505138

Electrical Ratings

Amperage Rating	3 A
Current / Amperage Rating	3 A
Current Rating	3 A
Voltage Rating	600V Max kV
Wattage	1800

Conductor Related

Conductor Size	#24 AWG
Conductor Type	Copper
Number of Conductors	3

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RFR303PE005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2035_INSTALLINST](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Sales Drawings - WDK_RFR303PE005_DRAWING_PDF](#)
- [Specifications - RFR303PE005](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)