



J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Almond

By Hubbell Wiring Device-Kellems
Catalog # [RJ620ALTR](#)



J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle,
Cat 6 Jack, F Coax, Decorator Frame, Almond

Application

Ideal for flat panels TVs

General

Color	<ul style="list-style-type: none">AlmondAmande
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device- Kellems
Temperature Rating	Per TIA
UPC	883778302572

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Certifications and Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - RJ620ALTR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2198_INSTALLINST](#)
[Sales Drawings - WDK_RJ620TR_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

[RJ620ITR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory](#)
[RJ620WTR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, White](#)
[RJ620LATR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Light Almond](#)
[RJ62ITR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Ivory](#)
[RJ600 - Net Select, JLOAD Box, Deep, Non-Metallic Clamps](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RJ620ALTR-SPEC-EN | REV 5/2023