

# J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Almond

By Hubbell Wiring Device-Kellems  
Catalog # [RJ650ALTR](#)

J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Almond



## Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

## General

Application	Ideal for flat panels TVs
Catalog Number	RJ650ALTR
Color	Almond
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	Per TIA
UPC	883778302459

## Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

## Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

## Certifications And Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - RJ650ALTR AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2198\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_RJ650TR\\_DRAWING\\_PDF](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)



A Hubbell brand