



J-Load Media Outlet, 15A 125V, Tamper Resistant Receptacle, 2-Port, Decorator Frame, Almond

By Hubbell Wiring Device-Kellems
Catalog # [RJ65ALTR](#)



J-Load Media Outlet, 15A 125V, Tamper Resistant Receptacle, 2-Port, Decorator Frame, Almond

Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

Application

Ideal for flat panels TVs

General

Color	Almond
Contact	Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Frame and Receptacle Only
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	Per TIA
UPC	883778302510

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
--------------	--------------------------------

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Installation Manuals - WIRING_PD2198_INSTALLINST](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

- [RU100SS - Under Cabinet Distribution Box, Slim, Metallic, Stainless Steel](#)
- [RJ600 - Net Select, JLOAD Box, Deep, Non-Metallic Clamps](#)
- [RU170W - Under Cabinet Distribution Box, Slim, Non-Metallic, Stainless Steel](#)
- [RJ620ITR - J-Load Media Outlet, 20A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Ivory](#)
- [RJ65ITR - J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-Port, Decorator Frame, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RJ65ALTR-SPEC-EN | REV 5/2023