

J-Load Media Outlet, 15A 125V
Tamper Resistant Receptacle, 2-
Port, Decorator Frame, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [RJ65ITR](#)

J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, 2-
Port, Decorator Frame, Ivory

Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

Application

- Ideal for flat panels TVs

General

Catalog Number	RJ65ITR
Color	Ivory
Contact	Brass
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Frame and Receptacle Only
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Temperature Rating	Per TIA
UPC	883778302541

Dimensions



Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
--------------	--------------------------------

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - Floorbox Selection Guide](#)
[Catalog Page - WDK Z-21 Catalog Page](#)
[Catalog Page - WDK Z-27 Catalog Page](#)
[Catalog Page - WDK Z-18 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2198_INSTALLINST](#)
[Specifications - RJ65ITR](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tamper-Resistant Receptacles](#)
[Video - Tradeselect Devices](#)