



Wiring Device-Kellems

Lamp Holders and Sockets, Mogul Base, 4KV Pulse Start, 12" Leads, Screw Mounted

By Hubbell Wiring Device-Kellems
Catalog # [RL4221](#)



Lamp Holders and Sockets, Mogul Base, 4KV Pulse Start, 12" Leads, Screw Mounted

Application

HID Incandescent

General

| | |
|------------------------------|---|
| Color | White |
| Item Type | Replacement Incandescent Lampholders |
| Lamp Size | Mogul Base |
| Material | Composite |
| Material - Mounting Hardware | Screw Mounting |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| Performance | <ul style="list-style-type: none"> Electrical - Rating - 1500W, 600V Max, 5KV Pulse Mechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire |
| Series | Lampholders |
| Type | HID Incandescent, Porcelain Keyless |
| UPC | 883778304033 |

Electrical Ratings

| | |
|---------------------------|------------|
| Amperage Rating | 2.5 A |
| Connectivity | 12" Leads |
| Current / Amperage Rating | 2.5 A |
| Current Rating | 2.5 A |
| Frequency Rating | 60 Hz |
| Voltage Rating | 600V AC kV |

Certifications and Compliance

| | |
|----------------------|-----------|
| Industry Standard(s) | UL Listed |
|----------------------|-----------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 10 |
|-----------------|----|

Product Assets

- [Catalog Page - Wiring_Catalog_CC8_CatPage](#)
- [Catalogs - Wiring Full Catalog](#)
- [Installation Manuals - WIRING_PD2362_INSTALLINST](#)
- [Sales Drawings - WDK_RL4221_DRAWING_PDF](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)



A proud member of the Hubbell Family.