



Incandescent Lamp Holders, Mogul Base, 5KV, 12" Wire Leads, Screw Mount

By Hubbell Wiring Device-Kellems
Catalog # [RL5221](#)



Incandescent Lamp Holders, Mogul Base, 5KV, 12" Wire Leads, Screw Mount

Application

HID Incandescent

General

Color	<ul style="list-style-type: none">• White• Blanc
Item Type	Replacement Incandescent Lampholders
Lamp Size	Mogul Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none">• Electrical - Rating - 1500W, 600V Max, 5KV Pulse• Mechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire
Series	Lampholders
Type	HID Incandescent, Porcelain Keyless
UPC	883778304057

Electrical Ratings

Amperage Rating	2.5 A
Connectivity	12" Leads
Current / Amperage Rating	2.5 A
Current Rating	2.5 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - Wiring_Catalog_CC8_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Installation Manuals - WIRING_PD2362_INSTALLINST](#)
[Sales Drawings - WDK_RL5221_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

[RL3742 - Lamp Holders and Sockets, Medium Base, Pre-Focus, 1000W 250V, Porcelain](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RL5221-SPEC-EN | REV 5/2023