



Lamp Holders and Sockets, Medium Base, Keyless, 600W 250V, 6" Leads, Plastic

By Hubbell Wiring Device-Kellems
Catalog # [RL8806](#)

Lamp Holders and Sockets, Medium Base, Keyless, 600W
250V, 6" Leads, Plastic



Application

Porcelain Lamp Holders, Medium Base

General

Color	White
Item Type	Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Lampholders
Type	Porcelain
UPC	883778112065

Electrical Ratings

Amperage Rating	2.64 A
Connectivity	6" Pigtails
Current / Amperage Rating	2.64 A
Current Rating	2.64 A
Frequency Rating	60 Hz
Voltage Rating	250V AC kV

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - Wiring_Catalog_CC6_CatPage](#)
[Catalogs - Wiring Full Catalog](#)
[Engineering Drawing - RL8806 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2478_INSTALLINST](#)
[Sales Drawings - WDK_RL8806_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

[RL106 - Incandescent Lamp Sockets, Pull Chain, Brass Shell, 600W 600V](#)
[RL8504 - Lamp Holders and Sockets, Medium Base, Keyless, 600W 600V AC, Terminal Screws, Plastic](#)
[RL8512 - Lamp Holders and Sockets, Medium Base, Pull Chain, 600W 250V, 2 Terminals, Plastic](#)
[RL102 - Lamp Holders and Sockets, Medium Base, Turn Knob, 2-Circuit, 660W 600V AC, Brass](#)
[RL105 - Incandescent Lamp Sockets, Push, Brass Shell, 600W 600V](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RL8806-SPEC-EN | REV 5/2023