



Wiring Device-Kellems

Lamp Holders and Sockets, Medium Base, Pull Chain, 600W 125V, 5-15R Receptacle, Terminal Screws, Porcelain

By Hubbell Wiring Device-Kellems
Catalog # [RL8822](#)



Lamp Holders and Sockets, Medium Base, Pull Chain, 600W 125V, 5-15R Receptacle, Terminal Screws, Porcelain

Application

Porcelain Lamp Holders, Medium Base

General

Color	White
Item Type	Incandescent Lampholders
Lamp Size	Medium Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Lampholders
Type	Porcelain
UPC	883778112096

Electrical Ratings

Amperage Rating	5.28 A
Connectivity	2) Terminal Screws
Current / Amperage Rating	5.28 A
Current Rating	5.28 A
Frequency Rating	60 Hz
Voltage Rating	125 VAC

Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog Page - Wiring_Catalog_CC6_CatPage](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - RL8822 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2478_INSTALLINST](#)
- [Sales Drawings - WDK_RL8822_DRAWING_PDF](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

- [RL8504 - Lamp Holders and Sockets, Medium Base, Keyless, 600W 600V AC, Terminal Screws, Plastic](#)
- [RL105 - Incandescent Lamp Sockets, Push, Brass Shell, 600W 600V](#)
- [RL8506 - Lamp Holders and Sockets, Medium Base, Keyless, 600W 600V AC, 6" Leads, Plastic](#)
- [RL106 - Incandescent Lamp Sockets, Pull Chain, Brass Shell, 600W 600V](#)
- [RL101 - Lamp Holders and Sockets, Medium Base, Turn Knob, 660W 600V AC, Brass](#)



A proud member of the Hubbell Family.