



Linkosity, 3A, 3W, Male Receptacle, 1'

By Hubbell Wiring Device-Kellems
Catalog # [RM0303PE001](#)



Linkosity, 3A, 3W, Male Receptacle, 1'

Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Male Receptacle
Material	Composite
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504254

Electrical Ratings

Amperage Rating	3 A
Current / Amperage Rating	3 A
Current Rating	3 A
Voltage Rating	600V Max kV
Wattage	1800

Conductor Related

Conductor Size	#24 AWG
Conductor Type	Copper
Number Of Conductors	3

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Product Assets

[Engineering Drawing - RM0303PE001 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2043_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_RM0303PE_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RM0303PE001-SPEC-EN | REV 5/2023