

Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V AC, PA Wire Code, 1' Length

By Hubbell Wiring Device-Kellems

Catalog # [RM1004PM005](#)



Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V AC, PA Wire Code, 1' Length

General

Application	Power and Control Integration
Catalog Number	RM1004PM005
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Male Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585131054

Electrical Ratings

Amperage Rating	10 A
Current / Amperage Rating	10 A
Current Rating	10 A
Voltage Rating	600V Max kV
Wattage	6000

Conductor Related

Conductor Size	#16 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RM1004PM005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2039_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Sales Drawings - WDK_RM1004PM005_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand