



Wiring Device-Kellems

# Linkosity, 20A 2W, Male Receptacle, 5'

By Hubbell Wiring Device-Kellems  
Catalog # [RM2002PE005](#)



Linkosity, 20A 2W, Male Receptacle, 5'

### Application

Power and Control Integration

### General

|                   |                               |
|-------------------|-------------------------------|
| Color             | Gray                          |
| Construction      | Fabricated                    |
| EU RoHS Indicator | Yes                           |
| Item Type         | Male Receptacle               |
| Material          | Composite                     |
| Number Of Poles   | 2-Pole                        |
| OEM Brand Name    | Hubbell Wiring Device-Kellems |
| UPC               | 783585409627                  |

### Electrical Ratings

|                           |             |
|---------------------------|-------------|
| Amperage Rating           | 20 A        |
| Current / Amperage Rating | 20 A        |
| Current Rating            | 20 A        |
| Voltage Rating            | 600V Max kV |
| Wattage                   | 12000       |

### Conductor Related

|                      |         |
|----------------------|---------|
| Conductor Size       | #12 AWG |
| Conductor Type       | Copper  |
| Number Of Conductors | 2       |

### Certifications and Compliance

|             |          |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

### Logistics

|                 |    |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

### Product Assets

- [Engineering Drawing - RM2002PE005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2033\\_INSTALLINST](#)
- [Literature - WIRING\\_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK\\_RM2002PE005\\_DRAWINGS\\_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.