

Linkosity, Male Receptacle, 20A 5W

By Hubbell Wiring Device-Kellems
Catalog # [RM2005PB010](#)



Linkosity, Male Receptacle, 20A 5W

Features

Linkosity20A 5W

Application

Power and Control Integration

General

| | |
|-------------------|-------------------------------|
| Catalog Number | RM2005PB010 |
| Color | Gray |
| Construction | Fabricated |
| EU RoHS Indicator | Yes |
| Item Type | Male Receptacle |
| Material | Composite |
| Number Of Poles | 5-Pole |
| OEM Brand Name | Hubbell Wiring Device-Kellems |
| UPC | 783585409481 |

Electrical Ratings

| | |
|---------------------------|-------------|
| Amperage Rating | 20 A |
| Current / Amperage Rating | 20 A |
| Current Rating | 20 A |
| Voltage Rating | 600V Max kV |
| Wattage | 12000 |

Conductor Related

| | |
|----------------------|---------|
| Conductor Size | #12 AWG |
| Conductor Type | Copper |
| Number of Conductors | 5 |

Certifications And Compliance

| | |
|-------------|----------|
| Nema Rating | Non-NEMA |
|-------------|----------|

Logistics

| | |
|-----------------|----|
| Carton Quantity | 50 |
|-----------------|----|

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RM2005PB010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2033_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Linkosity Wiring System](#)
[Sales Drawings - WDK_RM2005PB_DRAWING_PDF](#)
[Specifications - RM2005PB010](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Linkosity®](#)