



Wiring Device-Kellems

Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V AC, PA Wire Code, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [RM2303PB005](#)



Signal and Control, Linkosity, Male Receptacle, 3-Wire, 10A 600V AC, PA Wire Code, 1' Length

Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Male Receptacle
Material	Composite
Number Of Poles	3-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585524665

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number Of Conductors	3

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Engineering Drawing - RM2303PB005 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD1995_INSTALLINST](#)
- [Literature - WIRING_WLFVM034](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - Pulp & Paper Solutions](#)
- [Sales Drawings - WDK_RM2303_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.