

Signal and Control, Linkosity, Male
Receptacle, 4-Wire, 10A 600V AC,
PB Wire Code, 1' Length

By Hubbell Wiring Device-Kellems
Catalog # [RM3004PB001S](#)



Signal and Control, Linkosity, Male Receptacle, 4-Wire, 10A 600V
AC, PB Wire Code, 1' Length

Features

- Linkosity
- Male Receptacle
- 4-Wire
- 10A 600V AC

Application

Power and Control Integration

General

Catalog Number	RM3004PB001S
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Male Receptacle
Material	Composite with Stainless Steel Body
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585243313

Electrical Ratings

Amperage Rating	30 A
-----------------	------

Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V Max kV
Wattage	18000

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number of Conductors	4

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Specifications - RM3004PB001S](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Linkosity®](#)

