



Linkosity, Male Receptacle, 30A 4W

By Hubbell Wiring Device-Kellems
Catalog # [RM3004PB010](#)



Linkosity, Male Receptacle, 30A 4W

Application

Power and Control Integration

General

Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Male Receptacle
Material	Composite
Number Of Poles	4-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585504643

Electrical Ratings

Amperage Rating	30 A
Current / Amperage Rating	30 A
Current Rating	30 A
Voltage Rating	600V Max kV
Wattage	18000

Conductor Related

Conductor Size	#10 AWG
Conductor Type	Copper
Number Of Conductors	4

Certifications and Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Engineering Drawing - RM3004PB010 AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2035_INSTALLINST](#)
[Literature - WIRING_WLFVM034](#)
[Literature - Linkosity Wiring System](#)
[Literature - Pulp & Paper Solutions](#)
[Sales Drawings - WDK_RM3004PB010_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RM3004PB010-SPEC-EN | REV 5/2023