

Linkosity, Hazardous Location, Inlet, 5- Wire, 20A, Super Neutral, Isolated Ground

By Hubbell Wiring Device-Kellems

Catalog # [RM7205PB001](#)



Linkosity, Hazardous Location, Inlet, 5- Wire, 20A, Super Neutral,
Isolated Ground

General

Application	Power and Control Integration
Catalog Number	RM7205PB001
Color	Gray
Construction	Fabricated
EU RoHS Indicator	Yes
Item Type	Male Receptacle
Material	Composite
Number Of Poles	5-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585355658

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Voltage Rating	600V Max kV
Wattage	12000

Conductor Related

Conductor Size	#12 AWG, #10 AWG Neutral
Conductor Type	Copper
Number of Conductors	5

Certifications And Compliance

Nema Rating	Non-NEMA
-------------	----------

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RM7205PB001 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2316_INSTALLINST](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Linkosity Wiring System](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Sales Drawings - WDK_RM7205PB001_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand