



# TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

By Hubbell Wiring Device-Kellems  
Catalog # [RR151LAWRTR](#)



TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond

## Application

Residential Receptacles

## General

Color	Light Almond
Environmental Conditions	Weather Resistant
Item Type	Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> <li>Environmental - Operating temperature - -20°C to 60°C</li> <li>Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only</li> </ul>
UPC	883778302886

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

## Product Assets

- [Catalog Page - Wiring AA-17 Catalog Page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - RR151LAWRTR AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2131\\_INSTALLINST](#)
- [Literature - Residential Product Guide](#)
- [Literature - Residential Catalog](#)
- [Sales Drawings - WDK\\_RR151WRTR\\_DRAWING\\_PDF](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)
- [Video - Tradeselect Devices](#)
- [Video - Tamper-Resistant Receptacles](#)

## Related Products

- [P7LA - Wallplate, 1-Gang, 1.40" Opening, Light Almond](#)
- [RR151BKWRTR - TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Almond](#)
- [RR151LA - TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Single, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Light Almond](#)
- [RR151WRTR - TradeSelect, Straight Blade, Single Receptacle, Weather and Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Brown](#)
- [RR201LA - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Single, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Self Grounding, Light Almond](#)



A proud member of the Hubbell Family.