



# RESI DUP RCPT 15A 125V 8 HOLE PUSH GY

By Hubbell Wiring Device-Kellems  
Catalog # [RR15EGY](#)

RESI DUP RCPT 15A 125V 8 HOLE PUSH GY



## Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

## Application

Residential Receptacles

## General

Color	Gray
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778300912

## Dimensions

Display Size	Standard Sized Product
--------------	------------------------

## Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	5-15R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Engineering Drawing - RR15EGY AutoCAD Drawing](#)  
[Sales Drawings - WDK\\_RR15E\\_DRAWING\\_PDF](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)

## Related Products

[RR15SLAWRTR - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Weather and Tamper Resistant Duplex, 15A 125V, 5-15R](#)  
[SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)  
[RR15SGYWRTR - TradeSelect, Straight Blade Devices, Duplex Receptacle, Residential Grade, 15A 125V, 5-15R, Weather Resistant/Tamper Resistant](#)  
[RR15SGYTR - TradeSelect, Straight Blade, Duplex Receptacle, Tamper Resistant, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Gray](#)  
[RR15SIWRTR - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Weather and Tamper Resistant Duplex, 15A 125V, 5-15R](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-RR15EGY-SPEC-EN | REV 5/2023