

TradeSelect, Straight Blade, Duplex  
Receptacle, Tamper Resistant, Cut  
Ears, 15A 125V, 2-Pole 3-Wire  
Grounding, 5-15R, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [RR15KGYTR](#)



TradeSelect, Straight Blade, Duplex Receptacle, Tamper  
Resistant, Cut Ears, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R,  
Gray

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Trade-Select Devices

General

Catalog Number	RR15KGYTR
Color	Gray
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778301728

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Eight Push Wire Holes
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - RR15KGYTR AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2171\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_RR15KTR\\_DRAWING\\_PDF](#)  
[Specifications - RR15KGYTR](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)