



TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Self Grounding, White

By Hubbell Wiring Device-Kellems
Catalog # [RR15SW](#)



TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Self Grounding, White

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

General

Color	White
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
Performance	<ul style="list-style-type: none"> • Environmental - Operating temperature - -20°C to 60°C • Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only
UPC	883778100079

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Push and Side Wire
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - Wiring AA-16 Catalog Page](#)
- [Catalogs - Wiring Full Catalog](#)
- [Engineering Drawing - RR15SW AutoCAD Drawing](#)
- [Sales Drawings - WDK_RR15S_DRAWINGS_PDF](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)
- [Video - Tradeselect Devices](#)

Related Products

- [SS8 - Wallplates and Boxes, Metallic Plates, 1- Gang, 1\) Duplex Opening, Standard Size, Stainless Steel](#)
- [RR15SLATR - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Tamper Resistant Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R](#)
- [RR15SITR - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Tamper Resistant Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R](#)
- [P8W - Wallplate, 1-Gang, 1\) Duplex, White](#)
- [RR15SBKTR - TradeSelect, Straight Blade Devices, Receptacles, Residential Grade, Tamper Resistant Duplex, 15A 125V, 2- Pole 3-Wire Grounding, 5-15R](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RR15SW-SPEC-EN | REV 5/2023