



Wiring Device-Kellems

# CLOCK HANG RECESS RCPT, 20A 125V, SS

By Hubbell Wiring Device-Kellems  
Catalog # [RR201CHSS](#)

CLOCK HANG RECESS RCPT, 20A 125V, SS



## Application

Special Use Products

## General

Color	<ul style="list-style-type: none"> <li>Stainless Steel</li> <li>Acier inoxydable</li> </ul>
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778100475

## Dimensions

Display Size Standard Sized Product

## Electrical Ratings

Amperage Rating	20 A
Connectivity	Back and Side Wired Screw Terminals
Current / Amperage Rating	20 A
Current Rating	20 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	2500

## Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

## Certifications and Compliance

Nema Rating	5-20R
-------------	-------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Engineering Drawing - RR201CHSS AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2131\\_INSTALLINST](#)  
[Sales Drawings - WDK\\_RR201CHSS\\_DRAWING\\_PDF](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)

## Related Products

[RR151CHTR - TradeSelect, Straight Blade Devices, Tamper Resistant Receptacle, Clock Hanger, Residential Grade, 15A 125V, 2-Pole 3-WireGrounding, 5-15R, Ivory](#)  
[RR151OLA - RECESS TR DUP RCPT, 15A 125V, LG ALMOND](#)  
[RR151OI - RECESS TR DUP RCPT, 15A 125V, IVORY](#)  
[RR201CHWTR - TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, White Plate](#)  
[RR201CHBSTR - TradeSelect, Straight Blade, Single Receptacle, Clock Hanger, Tamper Resistant, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brass Plate](#)



A proud member of the Hubbell Family.