



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black

By Hubbell Wiring Device-Kellems
Catalog # [RRD151BK](#)



TradeSelect, Straight Blade, Single Decorator Receptacle, Self Grounding, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black

Application

Residential Receptacles

General

Color	Black
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	Decorator Single
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	883778100345

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase
Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Engineering Drawing - RRD151BK AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2131_INSTALLINST](#)
[Sales Drawings - WDK_RRD151_DRAWINGS_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

Related Products

[RRD201BK - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Black](#)
[RRD15BK - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Black](#)
[RRD15EBK - RESI DUP DEC RCPT 15A 125V 8 HOLE BK](#)
[RRD151W - TradeSelect, Straight Blade Devices, Residential Grade, Receptacles, Decorator Single, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, White](#)
[RRD205BK - TradeSelect, Single Decorator Receptacle, Self Grounding, 20A 250V, 2-Pole 3-Wire Grounding, 6-20R, Black](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-RRD151BK-SPEC-EN | REV 5/2023