

TradeSelect, Straight Blade Residential
Grade Receptacles, Weather and Tamper
Resistant Decorator Duplex, Self Grounding,
15A 125V, 5-15R, White

By Hubbell Wiring Device-Kellems
Catalog # [RRD15SWWRTR](#)

TradeSelect, Straight Blade Devices, Residential Grade, Receptacles,
Weather and Tamper Resistant Decorator Duplex, Self Grounding, 15A
125V, 2-Pole 3-Wire Grounding, 5-15R, White

Features

- Weather and Tamper Resistant Decorator Duplex
- Self Grounding
- 15A 125V

Application

Residential Receptacles

Specifications

Standards - RoHS Compliance	CM
Status	
Environmental Conditions	Weather Resistant
Nema Rating	5-15R
Conductor	
Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole
Current	
Amperage Rating	15 A
Voltage Rating Description	125 VAC
Current Rating	15 A

Voltage Rating	125 VAC
Wattage	1875 W
Connectivity	Push and Side Wire
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Display Size	Standard Sized Product
Weight	0.15 lb.

General

Color	White
UPC	883778303128
Material - Mounting Hardware	Screw Mounting
Item Type	Decorator Duplex
Material	Thermoplastic

Logistics

Pallet Quantity	9000
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)

