



## TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White

By Hubbell Wiring Device-Kellems  
Catalog # [RT100W](#)



TradeSelect, Cube Tap, 15A 125V AC, 2- Pole 3-Wire Grounding, 5-15R, White

### General

Color	White
Insulation	Insulated Body
Item Type	Adapters
Material	Composite
OEM Brand Name	Hubbell Wiring Device-Kellems
Operating Temperature	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Series	Taps & Adaptors
UPC	883778112461

### Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Voltage Rating	125 VAC
Wattage	1875

### Certifications and Compliance

Industry Standard(s)	C/US UL Listed
----------------------	----------------

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

[Catalog Page - Wiring\\_Catalog\\_CC10\\_CatPage](#)  
[Catalogs - Wiring Full Catalog](#)  
[Warranty - tradeSELECT™ and netSELECT®](#)

### Related Products

[RP648 - TradeSelect, Straight Blade Devices, Replacement Plug, 15A 125V, 2-Pole 2-Wire Grounding, 1-15P, White](#)  
[RT600I - TradeSelect, Cube Tap, Duplex to 6 Outlet, 15A 125V AC, 2-Pole 3-Wire Grounding, 5-15R, Ivory](#)  
[RP646 - TradeSelect, Straight Blade Devices, Residential Grade, Male Plug, 15A 125V, 2-Pole 2-Wire Non-Grounding, 1-15P, Polarized, 40" Cord](#)  
[RT300I - Adapters, Residential Grade, Single to 3 Outlet, 15A 125V 2-Pole 3-Wire Grounding, Ivory](#)  
[RT303 - Adapters, Heavy Duty Residential Grade, Single to 3 "X" Outlet, 15A 125V, 2-Pole 3-Wire Grounding, Ivory](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
WDK-RT100W-SPEC-EN | REV 5/2023