

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Liquid Tight Adapter

By Hubbell Wiring Device-Kellems
Catalog # [SAA34](#)

Heavy Duty Products, IEC Pin and Sleeve Devices, Industrial Grade, Accessories, Liquid Tight Adapter, For 16 and 20A 3 and 4-Wire, 3/4" NPT, Furnished with Hardware, Machined Aluminum

Features

- Industrial Grade
- Accessories
- Liquid Tight Adapter

Application

16 and 20 Amp, 3 and 4 Wire

Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 3,000V AC
- Electrical - Max Working Voltage - 600V AC RMS
- Environmental - Flammability - UL94-5VA and V-O classification
- Environmental - Ingress Protection - IP67 Suitability
- Environmental - Operating Temperatures - Maximum Continuous: 75° C
- Minimum Continuous: -40° C w/o impact
- Mechanical - Impact Resistance - In accordance with UL746C
- Mechanical - Product Identification - Identification and ratings are a part of the external label and molded into the receptacle mount
- Mechanical - Terminal Identification - Terminals identified in accordance with North American and International conventions

General

Catalog Number	SAA34
Color	Aluminum
EU RoHS Indicator	No
Environmental Conditions	Watertight
Item Type	Liquid-Tight Adapter
Material	Aluminum
Material - Mounting Hardware	Cord Mounted
OEM Brand Name	Hubbell Wiring Device-Kellems
Series	Accessories



Specifications

- Accessory Item - Conduit Adapter
 - Assembly Screws - Stainless Steel
 - Gaskets - Neoprene
 - Hinge Spring - Stainless Steel
- Style 3/4" NPT
Type Liquidtight Adapter
UPC 783585887159

Dimensions

Display Size Standard Sized

Electrical Ratings

Connectivity Pressure Terminal Screws

Conductor Related

Cord Type All Portable

Certifications And Compliance

Industry Standard(s) UL Listed
Nema Rating Non-NEMA

Logistics

Carton Quantity 5

Product Assets

[Catalog Page - WDK G-29 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_SAA34_INSTALLINST](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - Dual-Certified IEC Pin & Sleeve Devices](#)
[Sales Drawings - WDK_SAA34_DRAWING_PDF](#)
[Specifications - Wiring SAA34 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
WDK-SAA34-SPEC-EN | REV 4/2025