

Temporary Power, Spider Box, 30A  
125/250V, 3-Pole 4-Wire  
Grounding, Locking Receptacles,  
Yellow

By Hubbell Wiring Device-Kellems  
Catalog # [SDTL1A](#)



Temporary Power, Spider Box, 30A 125/250V, 3-Pole 4-Wire  
Grounding, Locking Receptacles, Yellow

Features

- Spider Box
- 30A 125/250V
- 3-Pole 4-Wire Grounding
- Locking Receptacles

Application

Heavy Duty Portable

General

Catalog Number	SDTL1A
Color	Yellow
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Item Type	Twist-Lock® Singles
Material	Thermoplastic
Material - Mounting Hardware	Non-Mounted, Portable
Number Of Poles	2-Pole
OEM Brand Name	Hubbell Wiring Device-Kellems
UPC	783585128702

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	30 A
Connectivity	Pre-Wired
Current / Amperage Rating	30 A
Current Rating	30 A
Phase	Single Phase
Voltage Rating	125 VAC
Wattage	3750

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#10 AWG

Certifications And Compliance

Nema Rating	6) L5-20R, 1) L15-30R
-------------	-----------------------

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - SDTL1A AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1989\\_INSTALLINST](#)
- [Literature - Safety Product Guide](#)
- [Literature - Education Application Guide](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK\\_SDTL1A\\_DRAWING\\_PDF](#)
- [Specifications - SDTL1A](#)
- [Warranty - Industrial & Commercial Products](#)