




Snap-Fit, Keystone, 3.5 MM Stereo Jack, Gold, Female to Female, Office White

By Hubbell Wiring Device-Kellems
Catalog # [SF35GFFOW](#)



Snap-Fit, Keystone, 3.5 MM Stereo Jack, Gold, Female to Female, Office White

Application

Snap-Fit 3.5mm Gold Audio Jack

General

Contact	Beryllium Copper
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Item Type	iSTATION AV Keystone Connections
Material - Mounting Hardware Style	Snap-On- Snap-Fit 3.5mm Pass-Thru, F/F
Temperature Rating	Per TIA
Type	Stereo Jack
UPC	662620211206

Dimensions

Display Size Standard Sized Product

Electrical Ratings

Connectivity	Female to Female
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Logistics

Carton Quantity 25

Product Assets

[Catalog Page - Wiring Z-8 Catalog page](#)
[Catalogs - Wiring Full Catalog](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs: 4, 6, 8 and 10 inch](#)
[Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Warranty - Industrial & Commercial Products](#)

Related Products

[SF35GFFOW - Snap-Fit, Keystone, 3.5 MM Stereo Jack, Gold, Female to Female, Office White](#)
[SFSPGR - Snap-Fit, Red Speaker Post, Office White](#)
[SF35GFFGY - Gold Stereo Jack, Snap-Fit, Keystone, 3.5 MM Stereo Jack, Female to Female, Gray](#)
[SF14SJOW - Snap-Fit, Keystone, 1/4" Stereo Jack, Office White](#)
[SF35GFFW - Gold Stereo Jack, Snap-Fit, Keystone, 3.5 MM, Female to Female, White](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WDK-SF35GFFOW-SPEC-EN | REV 5/2023